

Stall Layout Options

10' Wide Series

10×10 – (1) 10×10 stall

10×12 – (1) 10×12 stall

10×14 – (1) 10×14 stall

10×16 – (1) 10×10 stall; (1) 6×10 storage

10×18 – (1) 10×10 stall; (1) 8×10 storage

10×20 –

(2) 10×10 stalls

(1) 10×10 stall; (1) 10×10 storage

(2) 10×12 stall; (1) 8×10 storage

10×22 –

(1) 10×12 stall; (1) 10×10 stall

(1) 10×12 stall; (1) 10×10 storage

10×24 –

(2) 10×12 stalls

(1) 10×12 stall; (1) 10×12 storage

10×26 – (2) 10×10 stalls; (1) 6×10 storage

10x28– (2) 10×10 stalls; (1) 8×10 storage

10×30 –

(3) 10×10 stalls

(2) 10×10 stalls; (1) 10×10 storage

(3) 10×12 stalls; (1) 6×10 storage

10x32– (2) 10×12 stalls; (1) 8×10 storage

10x34– (2) 10×12 stalls; (1) 10×10 storage

10×36 –

(3) 10×12 stalls

(2) 10×12 stalls; (1) 10×12 storage

12' Wide Series

12×12 – (1) 12×12 stall

12×12 – (1) 12×12 stall

12×14 – (1) 12×14 stall

12×16 – (1) 12×12 stall; (1) 6×12 storage

12×18 – (1) 12×12 stall; (1) 8×12 storage

12×20 –

(2) 12×12 stalls

(3) 12x12stall; (1) 12×12 storage

(4) 12×12 stall; (1) 8×12 storage

12×22 –

(1) 12×12 stall; (1) 1212 stall

(3) 12×12 stall; (1) 12×12 storage

12×24 –

(2) 12×12 stalls

(4) 12×12 stall; (1) 12×12 storage

12×26 – (2) 12×12 stalls; (1) 6×12 storage

12x28– (2) 12×12 stalls; (1) 8×12 storage

12×30 –

(3) 12×12 stalls

(5) 12×12 stalls; (1) 12×12 storage

(6) 12×12 stalls; (1) 6×12 storage

12×32 – (2) 12×12 stalls; (1) 8×12 storage

12×34 – (2) 12×12 stalls; (1) 12×12 storage

12×36 –

(3) 12×12 stalls

(4) 12×12 stalls; (1) 12×12 storage